

1+1 cork stopper

44 x 23,7 mm

Product description

NORMATIVE

Length	44 mm ± 0,5 mm	
Diameter	23,7 mm ± 0,3 mm	
Ovalization	< 0,3 mm	UNE 56926
Wash	Peroxide	
Disk Thickness	≥ 4,0 mm	

Physical and Mechanical Characteristics

NORMATIVE

Humidity	4.0 – 8 %	
Density	235 - 315 Kg/m ³	UNE 56926
Extraction Strength	15 daN- 45 daN	
Capillarity	< 2,5 mm	UNE 56926
Tightness	100 % no leakage at 2.5 bar, in internal Ø 18,5 mm tubes	UNE 56934

Chemical, microbiological and sensory characteristics


NORMATIVE

Dust residues	≤ 0.001 g / cork stopper	UNE 56926
Oxidising residues (O₂²⁻)	< 0.2 mg / cork stopper	UNE 56926
Sensory analysis	Without sensory desviations	UNE 56928
Fungus and yeasts	< 10 U.F.C / cork stopper	
Aerobic mesophilia bacteria	< 30 U.F.C / cork stopper	UNE 56926
TCA	<0,9 ng/L	

Recommendations

- Ideal storage temperature between 15 and 20°C, in dry, odor-free and ventilated store .
- Appropriate relative humidity between 40 and 70%.
- Cork stoppers are recommended to be used in a maximum period of 6 months from manufacture date.
- Empty corks feeding hopper after each bottling.
- Do not open the bags until the stoppers are used. Do not leave bags open with leftover corks. Close the bag.
- Cork stoppers should be treated as a food product and should not be stored with chemicals or others giving off odors.
- Processes and products used in their manufacture comply with the International Code of good cork stoppers Practices and EC 2023/2006.

C/ Iturrizar, 3 - 31131 CIRAQUÍ (Navarra) España
Tel. +34 948 34 21 49 - Fax +34 948 34 21 48
ebro cork@ebro cork.com www.ebro cork.com



C/Iturrizar, 3 - 31131 Ciraquí (Navarra)
Tel. 948 34 21 49 - Fax. 948 34 21 48
ebro cork@ebro cork.com
CIF: B-31742794

BRCS
Packaging Materials
CERTIFICATED

LRQA
CERTIFIED
ISO 9001

UKAS
CERTIFIED
ISO 9001

C O R K